

PETG Protective Divider

1/4" Thick Clear PETG Construction

Instruction Manual

Thank you for your purchase of the Larson Electronics XLE-MD-PCD Series PETG Protective Divider. Please read these instructions before installing your divider, and retain for future use.

The XLE-MD-PCD Series from Larson Electronics is a PETG Divider that helps to protect people and employees by adding a clear barrier. This divider is ideal for use at banks, government agencies, hospitals, cafeterias, break rooms, restaurants and anywhere else where interaction happens and/or social distancing is a challenge to accomplish.

The XLE-MD-PCD Series protective divider is constructed from 1/4" thick PETG that is both durable and easy to clean. The PETG is clear and easy to see through as well as being more impact resistant than glass. No tools are required to assemble this sneeze guard. The hanging model is a single piece requiring no assembly, and the desk model has pieces that simply snap together for easy and fast assembly. Unlike polycarbonate, PETG is food grade safe.

Installation

The XLE-MD-PCD Series protective divider is designed for fast and easy installation. The hanging model has two mount holes at the top corners for hanging the divider from the ceiling or wherever else you wish to hang it. Hardware is not provided for hanging. Be sure the divider is hung in a location that is capable of supporting the weight of the divider. The desk divider comes with two leg pieces that simply snap together via slots at the bottom side of the divider, allowing the divider to stand on a desk, table, or other flat surface.

Use and Care

The XLE-MD-PCD Series protective divider requires no maintenance, but should be cleaned with a non corrosive cleaner and a soft cloth as needed. Periodically check the mount locations for hanging models to be sure the divider is still secure, and rehang if necessary.



THESE INSTRUCTIONS MAY NOT COVER ALL DETAILS OR VARIATIONS OF THIS PRODUCT FOR YOUR EQUIPMENT OR INSTALLATION REQUIREMENTS. SHOULD FURTHER INFORMATION NOT COVERED BY THESE INSTRUCTIONS BE REQUIRED, PLEASE CONTACT LARSON ELECTRONICS BY EMAIL AT SALES@LARSONELECTRONICS.COM OR BY PHONE AT 1-800-369-6671 FOR FURTHER ASSISTANCE.

PLEASE VISIT LARSONELECTRONICS.COM FOR **WARRANTY** AND **RETURN** INFORMATION.